

QSil 217

Transparent, Liquid Silicone Rubber

PRODUCT DESCRIPTION

QSil 217 is a two-part, clear, liquid silicone that will cure at room temperature or at elevated temperatures. It has a low viscosity, which allows for ease of flow around complex parts, providing electrical insulation and shock resistance. The chemical composition provides hydrolytic and reversion resistance.

KEY FEATURES

- Convenient 1:1 mixing ratio for use in automatic dispensing equipment or hand mixing
- Contains no solvents
- Non-yellowing catalyst system

TYPICAL PROPERTIES

UNCATALYZED				
TEST	QSil 217 A	QSil 217 B		
Color	Clear	Clear		
Viscosity	360 cps	300 cps		
Specific Gravity	0.97	0.97		

CATALYZED		
MIX RATIO 1:1 by weight		
Color	Clear, colorless	
Consistency	Easily pourable	
Gel time at 25°C *	20 minutes	

* Gel time is defined as the time required for the material to become a solid or a semi-solid.

CURED PROPERTIES		
60 minutes at 100°C/212°F		
PROPERTY	RESULT	
Durometer, Shore A	35	
Linear shrinkage	< 0.1 %	
Refractive index	1.406	



ELECTRICAL PROPERTIES		
Dielectric strength	480 V/mil	
Dielectric constant @ 1000 Hz	3.00	
Dissipation factor @ 1000 Hz	0.002	
Volume resistivity	1.0 X 10 ¹⁵ ohm-cm	

THERMAL PROPERTIES			
Useful temperature range	- 55°C – 204°C		
Thermal conductivity	0.18 W/m-K		
Coefficient of thermal expansion, cm/cm, °C	28.0 x 10 ⁻⁵		
Specific heat	0.3 cal/g-C		

MIXING

QSil 217 A is catalyzed with QSil 217 B at a 1:1 ratio by weight. In order to achieve optimum performance the same lot number of QSil 217 A and QSil 217 B should be used.

Combine one part of QSil 217 A with one part of QSil 217 B by weight into a clean, compatible container. The volume of the container should be 3-4 times the volume of the material to be mixed. Mix by hand or with mixing equipment until a homogeneous mixture is obtained. Accurate weighing of all components, on a suitable scale, is essential for optimal product performance when mixing by hand.

DE-AERATION

Air trapped during mixing should be removed by vacuum at 29 inches of mercury. During the process the material will expand and intermittent evacuation may be required. Typically after releasing the vacuum 2 - 3 times the mass will collapse on itself at which time the vacuum should be left on for an additional 2 - 4 minutes.

Machine mixed material does not normally need to be de-aired.

STORAGE AND SHELF LIFE

If QSil 217 A and QSil 217 B are stored in their original unopened containers, in an environment that does not exceed 38°C (100°F) then QSi will warranty the material for a period of 12 months from the date of shipment.

Technical Data Sheet



DISCLAIMER

The technical data listed is provided for reference only and is not intended as product specifications. QSi has the capability to customize products as requested. For sales and technical assistance please contact customer service at (804) 271-9010 or 1-800-852-3147.

Please be sure to visit our website daily for our complete product portfolio, new product introductions and more! <u>www.quantumsilicones.com</u>

> Quantum Silicones Headquarters 7820 Whitepine Road Richmond, VA 23237

Manufacturing, Research and Development Facility 8021 Reycan Road Richmond, VA 23237

> Phone: 804-271-9010 Fax: 804-271-9055 Toll Free: 800-852-3147